

High pressure steamer

Model VBD 7

For steaming of vamps before crimping

Correct steaming of vamps on our new damping unit model VBD 7 before crimping.

Advantages:

- short damping and moistening of the vamps within 2 - 5 seconds before the crimping process
- no cracking of the upper leather by correct adjustment
- no inconvenience caused by steam clouds because the steam is only flowing when needed
- all parts that get into contact with damp are made of non-rusty material.

Serial equipment:

Electronic heating regulation for upper mould

Electronic heating regulation for lower mould

Time adjustment for steaming period for upper mould

Time adjustment for steaming period for lower mould

Valves to adjust the steam quantity of:

Upper mould

Lower mould

Technical details:

length, width, height

packing dimensions

electrical supply

electrical contact

pneumatical contact

air consumption per pair

weight gross (crate)

weight net

Typ VBD 7

500x670x1450

650x850x1700

240 V 50 Hz

6 kW 16 Amp

1/4"

0,5 Ltr./ Takt

170 Kg

120 Kg

